




Merit LILIN Application Note LILIN OSD Focus Assistant (FA) for HD Cameras

Document Number : A00061
Date : 2014/12/05
Dept : Technical Support, Taipei

Subject: LILIN adopts OSD focus assistant (FA) technology for all vari-focal cameras of L series, Pro series, Ultra series, and 4K series

Focusing HD vari-focal camera can be a time consuming task. With the new firmware version 1.4.36 or above, focus assistant can save installation time and cost.



To enable focus assistant feature, click on FA button on the web interface of the camera. The FA OSD appears.



The C and O symbols represent (C) the current sharpness value and (O) the historical optimized sharpness value. During the process of adjusting the focal ring of the HD camera, C value represents current sharpness. (O) is the best historical sharpness value while focusing far and/or near.

With the latest FA technology, you can easily focus a HD camera by matching the (O) value during focusing process.

Note: The FA OSD automatically disappears one minute later.